

Фильтрующие вентиляционные безопасные шкафы диапазон 14.X

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижегород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: efj@nt-rt.ru || сайт: <https://ecosafe.nt-rt.ru>

FILTERING VENTILATION SECURE CABINETS



▲ AF5-2X + CORG51



▲ AF3X + CORG51



▲ AFP5-2X + CORG51



▲ AFP3X + CORG51

COMPLIANCE

- Adsorption capacity of active charcoal filters and filtration system tested to NF X 15-211 - May 2009.
- Complies to articles R.5132-66 and R.5132-68 of the Public Health Code.
- Complies with recommendation for risk prevention and safety.
- Standardized warning labels in accordance with ISO 3864 standard, and with European Directive 92/58/EEC.
- Electric fan conforms to CE specifications.

ADVANTAGES

- **Labopur®** technology.
- Available in 2 versions: Steel doors or glass doors.
- Self-contained cabinets for your safety.
- Elimination of dangerous vapors.
- No connection or evacuation required, no civil engineering solution.
- Ventilation system operation indicator light.
- Window for checking the presence of the filter adapted to your needs.
- Active charcoal filter for organic vapors or high efficiency polyvalent active charcoal filter(1) tested to NF X 15-211 standard.
- Anti-dust filter, 92% efficiency against particles > 3 µm.
- Easy replacement of the active charcoal filter.
- Hour meter permanently indicating the total duration of use of the cabinet. After programming, every 60 hours, an audible

signal indicates that the active charcoal filter needs to be checked for saturation.

TECHNICAL CHARACTERISTICS

- 10/10 steel construction.
- White epoxy paint RAL 9010.
- Standardized warning labels for «Flammable», «Corrosive», «Toxic» or «Harmful» products.
- Height-adjustable containment shelves on rack.
- Removable Containment sumps in the lower part, height 100 mm.
- Independent storage compartments for AFP5-2X and AF5-2X models.
- Hinged doors with key lock.
- Top and bottom ventilation:
 - Air inlet with double grille at the bottom of the doors.
 - Roof outlet Ø 100 mm with grilles.

ventilation box:

- Silent fan: CE 220-240 volts - 50 Hz; 86 m3/hour flow rate; 0.1 A, 20 watt; 43 dB(A) sound level (excluding air flow) with plug and electric cable - IP54 protection.
- Casing to be equipped with a molecular filter ORG50 or CORG51 for indoor discharge, or with a kit for use without active charcoal filter (CAR50) for outdoor connection.



OPTIONS

- Additional shelf EE1 or EE2.
- Active charcoal filters: The cabinets are delivered without active charcoal filters. You must select one from the table below depending on the type of products you are storing. See table.
- PVC containment shelf and containment sump for corrosive products. SEPVC, SBPVC.

- Sampling port in the front.
- Sampling port for the introduction of specialized reagent tubes.
- Use of a manual pump.
- Detection of the efficiency or saturation of the active charcoal filter by reading the tubes.

Absorbent mats to be placed at the bottom of the containment sump (supplied in packs of 10 sheets reference JF10D).

Filter saturation level control by REACTIVE TUBES:

CABINETS TO BE FITTED WITH A FILTER

| P/N | Description | Dimensions H x W x D (mm) | Storage capacity (L) | Containment capacity (L) | Number of shelves | Weight (kg) |
|---------|--|--|----------------------|--------------------------|-------------------|-------------|
| AFP3X | Filtering ventilation cabinet with steel door | Ext. 2135 x 560 x 545 Int. 1795 x 555 x 480 | 150 | 41 | 3 | 75 |
| AF3X | Filtering ventilation cabinet with glass door | Ext. 2135 x 560 x 545 Int. 1795 x 555 x 480 | 150 | 41 | 3 | 75 |
| AFP5-2X | Filtering ventilation cabinet with steel doors | Ext. 2135 x 1110 x 545 Int. (2x) 1795 x 555 x 480 | (2x) 140 | (2x) 41 | 6 | 130 |
| AF5-2X | Filtering ventilation cabinet with glass doors | Ext. 2135 x 1110 x 545 Int. (2x) 1795 x 555 x 480 | (2x) 140 | (2x) 41 | 6 | 130 |

ACTIVE CHARCOAL FILTER AND ACCESSORIES

| P/N | Description | Dimensions H x W x D (mm) | Containment capacity (L) | | Weight (kg) |
|--------|---|---------------------------|--------------------------|-------------------------------------|-------------|
| CORG51 | Multi-purpose active charcoal filter ⁽¹⁾ | 70 x 390 x 390 | - | To be changed at least once a year. | 9 |
| ORG50 | Active charcoal filter for organic vapors | 70 x 390 x 390 | - | | 8 |
| FOR50 | Active Charcoal Filter for formaldehyde vapors | 70 x 390 x 390 | - | | 8 |
| CAR50 | Kit for using without filter | | | | 4 |
| PMAF | Manual pump for reagent tubes | | | | 0,4 |
| TROR | 10 reagent tubes for "organic" tests | | | | 0,1 |
| TRAC | 10 reagent tubes for "corrosive" tests | | | | 0,1 |
| TROA | 5 reagent tubes for «organic» tests and 5 reagent tubes for «corrosive» tests | | | | 0,1 |
| EE1 | Additional containment shelf for AFP3X and AF3X | 22 x 550 x 465 | 5 | - | 5 |
| EE2 | Additional containment shelf for AFP5-2X and AF5-2X | 30 x 545 x 470 | 7 | - | 5 |
| SEPVC | PVC additional containment shelf | 20 x 525 x 455 | 5 | - | 4 |
| SBPVC | PVC containment sump | 90 x 535 x 465 | 24 | - | 3 |
| JF10D | Absorbent mats (pack of 10 sheets) | | | | 1 |

(1) CORG multipurpose active charcoal filters can adsorb the vast majority of commonly used products: corrosive products, organic compounds or solvents.

N.B : Refer to the table of chemical incompatibilities and precautions for use, to validate the configuration of your cabinet according to your needs.

Fume hoods, filtering cabinets - Ventilation

Lithium-ion cabinets

Flammable cabinets

Corrosive cabinets

Toxic cabinets and Multirisk

Containment and cans

File cabinets Anti-fire equipments

Showers and first-aid equipments

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: efj@nt-rt.ru || сайт: <https://ecosafe.nt-rt.ru>